



## The LND-PKD310

PEAK SAMPLE & HOLD WITH OFFSET + AMPLIFIER

### The LND-PKD310 Peak Sample & Hold with Offset + Amplifier

What is the LND-PKD310?

The LND-PKD310 is a versatile peak sample and hold IC with digitally programmable gain (1-16x), two DC level shifters, and very accurate peak detect circuit. All functions of this IC are controlled by microcontroller; this product is considered a microcontroller peripheral device.

How does it work?

- Connect Vcc and Gnd, connect the clock signal.
- Reset the device by holding M and D low for at least 64 clock cycles. This will clear all registers.
- Load level shift registers A and B, and set the programmable gain on the opamp.
- Connect input signal to In.
- Initiate sample and hold with microcontroller, the resulting peak value will be on Out.
- Ensure that the sample time is long enough to ensure that a full waveform passes through the device.

How Do I get samples?


The LND-PKD310 is available in 28 pin ceramic package. For volume orders, Linear Dimensions can package this device in industry standard packaging including a SOIC-28. Please contact your Linear Dimensions representative for more information or [www.lineardimensions.com](http://www.lineardimensions.com).

### Features

- Accurate Peak Detect
- Programmable DC Gain
- Two DC Level Shifters
- All Functions Digitally
- Controlled Including
- Clcking of Sample & Hold

### Applications

- Sensor Arrays
- Security Monitors
- Input Devices
- EmbeddedControllers
- Microncontroller Peripheral



The sum is done in the gain stage, so the signal won't rail internally.

There are 5 internal registers to control MUX address, filter tuning, signal gain, and DAC settings.